

## Zehnder ComfoAir Q350 Complete ERV Kit



**Brand:** Zehnder  
**Product Code:** 9668-01-Q350-Kit2  
**Weight:** 0.00kg  
**Dimensions:** 0.00cm x 0.00cm x 0.00cm

**Price: \$11,079.15**

### Short Description

The **Zehnder ComfoAir Q350 Complete ERV Kit** is a high-efficiency ventilation solution designed for medium to large homes and small commercial spaces from **1,600 to 2,300 sq.ft.**. This 6-inch system delivers balanced indoor air quality, recovering heat and moisture for superior comfort and energy savings. Perfect for moderately sized spaces, the Q350 kit includes all components for a seamless installation. The kit provides all essential parts for a **complete setup, covering ventilation, controls, ducting, and filtration.**

### Description

Q350 Energy Recovery Ventilation System Parts List

#### Q350 Energy Recovery Ventilation System Parts List

##### Detailed Parts List - Q350 Energy Recovery Ventilation System 6"

1. Ventilation Unit 2. Controls 3. ComfoPipe & Grills 4. ComfoWell 5. ComfoFresh Ducting 6. Register Boxes 7. Register Covers 8. Filtration

Control-ComfoConnect-Lan

C

Comp-Bath Boost Switch-

Wired

---

ComfoWell-End

Plate-4x2-160mm

ComfoWell-Manifold-4x2-T

---

Register-Round-3x1

---

Filter-Q-Set-G4/F7

---

```
function openTab(evt, sectionName) { // Hide all tab contents var tabContents = document.getElementsByClassName("tab-content"); for (var i = 0; i
```

---

## Instructions for Additional ComfoPipe

---

Q350 Measurement Guide

### Important: Measure Before Installation

To ensure proper installation of your Q350 Energy Recovery Ventilation System, accurate measurement of your specific installation requirements is essential. The quantities listed in our standard package are estimates and may need adjustment based on your building's layout.

**?? Please Note: The standard package includes estimated quantities of ComfoPipe components. You may need additional components based on your specific installation requirements.**

### Measurement Steps:

1. Determine the exact locations for your intake and exhaust connections
2. Measure the total straight line distance needed for all ComfoPipe runs
3. Count the number of turns required and determine the angles needed
4. Add approximately 10% extra length to account for cutting waste and adjustments

**? Tip: For most installations, you'll need additional ComfoPipe sections beyond the standard package. One meter sections can be easily cut to your exact specifications.**

**Standard Package Components:**

| SKU     | Description                              | Quantity |
|---------|------------------------------------------|----------|
| 9631-00 | Duct-ComfoPipe-160mm-1m                  | 10       |
| 9632-00 | Duct-ComfoPipe-160mm-45°                 | 8        |
| 9633-00 | Duct-ComfoPipe-160mm-Directional Coupler | 2        |

**How to Adjust Your Order:**

After measuring your specific requirements, you may need to add additional components to your cart:

- For additional straight runs: Add more "Duct-ComfoPipe-160mm-1m" units
- For additional turns: Add more "Duct-ComfoPipe-160mm-45°" units
- For additional directional couplers: Add more "Duct-ComfoPipe-160mm-Directional Coupler" units

[Add Additional ComfoPipe Components](#) [Add Additional ComfoPipe 45°](#) [Add Additional Directional Coupler](#)

If you need assistance with calculating the correct quantities for your installation, please contact our technical support team.

**Additional ComfoTube**

ComfoFresh Ducting: Accurate Measurement Required

The ComfoFresh Ducting system connects your ComfoWell manifold to the individual room terminals. Proper measurement of your specific requirements is crucial for a successful installation.

?? Important: The standard package includes 2 rolls (162.5ft each) of ComfoTube 75 ducting. You must verify if this quantity is sufficient for your specific building layout before proceeding with installation.

**How to Calculate Required Ducting:**

1. Map out the precise location of each supply and exhaust terminal
2. Measure the path from each terminal to the ComfoWell manifold
3. Account for bends and routing around obstacles (add 1ft per bend)
4. Sum all paths to determine total required length
5. Add 15% extra for cutting waste and potential route changes

**? Pro Tip:** Keep ducting runs as short and straight as possible. Each 10 feet of additional duct length or bend creates resistance that can reduce airflow efficiency.

**Standard Package Component:**

| Article No. | Description                  | Quantity | Unit Price | Total    |
|-------------|------------------------------|----------|------------|----------|
| 9272-00     | Duct-ComfoTube<br>75-162.5ft | 2        | \$374.00   | \$748.00 |

**Common Installation Scenarios:**

| Home Size                | Typical Rooms  | Estimated Ducting | Rolls Needed |
|--------------------------|----------------|-------------------|--------------|
| Small (<1500 sq ft)      | 6-8 terminals  | 180-240 ft        | 2 rolls      |
| Medium (1500-2500 sq ft) | 8-12 terminals | 280-360 ft        | 3 rolls      |
| Large (2500+ sq ft)      | 12+ terminals  | 380+ ft           | 3+ rolls     |

**Need Additional Ducting?**

**Based on your measurements, if you require additional ComfoTube ducting:**

- Each roll contains 162.5 feet of flexible ducting
- Additional O-rings (item 9274-00) may be needed for connections
- Consider ordering extra coupling pieces (item 9273-00) for longer runs

### Add Additional ComfoTube

For assistance with calculating your specific ducting requirements, please contact our ventilation design specialists at.

